

Detailed Capabilities Overview

January 2018

Distribution A: Approved for Public Release

2021 Girard Blvd. SE, Suite 150 Albuquerque, NM 87106 505-245-9970

An Employee-Owned Company

1360 Technology Ct, Suite 200 Dayton, OH 45430 937-684-4100



Export Control Guidelines

- The following presentation provides information regarding MZA general capabilities and basic marketing details, general system capabilities, simulated results, notional graphs and data from the public domain or other materials cleared for public release about products that are classified as ITAR or publically available under the EAR.
- Commodity Jurisdiction determinations have established that the Atmospheric Turbulence Profilers and Diagnostic products are regulated by the EAR and most are classified as EAR99. Commodity Jurisdiction determinations have established that various adaptive optics components including deformable mirrors and wavefront sensors are designated as defense articles under Category XVIII(e) of the United States Munitions List (USML).
- MZA Associates Corporation deems the content of this presentation to be nonproprietary and not subject to either the ITAR based on releases at ITAR 120.10 (b) and 120.11 or the EAR Part 732 and 734.3(b)(3)/734.7.



- MZA is a small business that specializes in the modeling, simulation, and analysis (MS&A), design, development, engineering, and testing of advanced optical and control systems for High Energy Laser Weapon Systems (HELWS) and advanced surveillance systems (ISR).
- MZA has provided more than twenty-five years of support to a broad range of US Department of Defense (DoD) research organizations and provides some of the most formidable capabilities in the concept development, analysis, modeling, systems engineering, manufacturing, integration and test of HELWS.
- MZA's staff consists of some of the world's experts in the fields of advanced beam control analysis and design, beam control component and system development, aero-optical and aeromechanical effects, atmospheric propagation, and laser engagement analysis.
- No other single organization of any size provides equivalent breadth and depth of engineering, analysis, and manufacturing capabilities for HELWS beam control systems.



MZA's Core Capabilities

Laser Weapon & Optical Sensing Modeling & Simulation

- WaveTrain Integrated physics-based simulation
- O Atmospheric and aero-effects modeling
- **O** Beam control and propagation scaling models
- **O** Systems engineering models
- **O** Laser resonator device modeling

• Laser System Design, Development, Integration & Testing

- O Beam Control
- \mathbf{O} Imaging
- O Laboratory and field experimentation
- O Experimental analysis
- **O** Turbulence profiling
- O Aero optics

Adaptive Optics & Beam Control Hardware


- O High-speed tracking and wave front compensation devices
- O High Power Deformable Mirrors (HPDMs)
- O Real-time and distributed control systems
- O Optical telescopes and beam directors
- **O** Experimental optical measurement devices
- **O** Atmospheric measurement devices

MZA is a world leader in the modeling, analysis, and development of directed energy and imaging systems

- Beam control and imaging systems
- Adaptive optics design and implementation
- Atmospheric and aero optical effects
- High energy laser systems engineering
- Target signatures and vulnerability
- High speed target tracking
- Laser communications
- LADAR/LIDAR applications
- Deformable mirrors and wavefront sensors

MZA's modeling and analysis software has been used on nearly every major HEL program of the past twenty years.






ABL

NOP




RDS






February 11, 2010 First Boost-Phase Ballistic Missile Shootdown









ED



- Navy Fixed-Wing Demonstrator (AeroFWD, ONR/NAVAIR)
- Self-Protect High Energy Laser Demonstrator Advanced Technology Demonstration (SHiELD ATD, AFRL)
- Mobile Beam Control System Integration Laboratory (MBCSIL, SMDC)
- Helicopter Beam Director for High Energy Fiber Laser (HEFL HBDS, ONR)
- Demonstrator Laser Weapons System (DLWS, AFRL/DARPA)
- High Energy Liquid Laser Area Defense System (HELLADS, DARPA)
- Airborne Aerooptics Laboratory (AAOL, HEL-JTO)
- High Energy Laser Mobile Test Truck (HELMTT, SMDC)
- Next Generation Airborne Laser (NGABL, MDA)
- WSMR Solid State Laser Test Bed (SSLTB, SMDC)
- Airborne Laser Test Bed (ALTB, MDA)
- Robust Electric Laser Initiative (RELI, HEL-JTO)
- Joint High Power Solid State Laser (JHPSSL, HEL-JTO)
- High Energy Laser Future Air Demonstration (HELFAD, AFRL)
- Tactical Relay Mirror System (TRMS, AFRL)



MZA's Major & Recurring Customers

- Air Force Research Laboratory (AFRL/RD-RY-RQ-RV)
- High Energy Laser Joint Technology Office (HEL-JTO)
- Missile Defense Agency (MDA)
- Defense Advanced Research Projects Agency (DARPA)
- Naval Air Systems Command (NAVAIR)
- Army Space & Missile Defense Command (SMDC)
- Office of Naval Research (ONR)
- Arnold Engineering Development Center (AEDC)
- Naval Research Laboratory (NRL)
- Air Force Institute of Technology (AFIT)
- Naval Postgraduate School (NPS)
- US Aerospace and Defense Contractors

Lockheed Martin, General Atomics, Textron, Raytheon, SAIC, Leidos, Boeing, Schafer, Parsons, Radiance, Kratos

• US Educational Institutions

Notre Dame, U of Dayton, UCLA, U of MD, U of Central FL



Overview of Hardware Development Efforts





Optimized Tactical High Energy Laser Architecture

Lightweight Compact Beam Directors

Addressing a high priority need identified by the Air Force Research Laboratory, MZA undertook the challenge to develop lightweight compact beam directors for high power laser applications.

The result has been the development of MZA's Othela line of beam directors that utilize the latest technologies in opto-mechanical materials, gimbals, optical coatings, and sensors to reduce the number of high power optics in order to institute on-gimbal beam control concepts.


- Integrated on-gimbal beam control systems.
- Line-of-site stabilization and wave front compensation.
- < 1 cubic meter in volume
- < 500 lbs.
- Designed for high power laser applications.
- On-axis and off-axis telescope designs.





High Energy Fiber Laser (HEFL) Helicopter Beam Director System (HBDS)

See movie at: https://www.youtube.com/watch?v=Bgc4YCVcJ9g&feature=youtu.be



4) urad —

- Fine Sensor

Nose

74.05 AZ 0.04 EL HBDS

FC State #20

Offset:



HELWS Concept Engineering





DELTA

PM-02-600

MZA's Delayed Tilt Anisoplanatism (DELTA) method measures

turbulence strength along a line of sight. These turbulent

fluctuations, commonly observed as twinkling of distant lights or

stars, significantly affect high resolution imaging sensors and can

reduce efficiency of laser beam projection for illumination and

optical communications. The same phenomena also give insight

into other aspects of the atmospheric path, including evapo-

transpiration measures critical to water and agricultural

Description

management activities.

Operation

- MZA manufactures atmospheric profiling devices that can be used to establish requirements for ISR and beam control system performance.
- The techniques utilized have been proven in multiple experiments.

Path-Resolved Optical Profiler System (PROPS), PR-05-600



Laser propagation path characterization

Optical communications link performance

Evapo-transpiration and water management

Include profiles in wave-optics simulations

• Atmospheric imaging diagnostics

Enables custom MATLAB analysis

Applications

Operation


Description

MZA's Path-Resolved Optical Profiler System (PROPS) measures turbulence strength along a line of sight. Turbulent wavefront measurements are sampled with a telescope-mounted sensor on both sides of the propagation path from multiple sources, from which C22 is derived. These turbulent fluctuations significantly affect high resolution imaging sensors and can reduce efficiency of laser beam projection for directed energy, illumination and optical communications. The same phenomena also give insight into other aspects of the atmospheric path, including evapo-transpiration measures critical to water and agricultural management activities.

Unique Advantages

- Resolves C² turbulence strength along path
- · Automatic computation of:
 - Rytov number Scintillation index
 - Fried's coherence diameter
 - Isoplanatic angle
 - Cross-wind speeds
 - Greenwood and Tyler frequencies
- Time-resolved wavefront measurements 5+ km range between terminals
- Automatic collection, processing, & reporting
- Operator data quality feedback
- · Eye-safe, non-laser sources
- Output supports ATMTools and WaveTrain

Identical PROPS optical transceiver terminals are placed on each side of a propagation path which typically extends up to 5 km or longer given favorable atmospheric transmission. The terminals transmit multiple wavelength sources and image each source with sensitive cameras which record the deviation or "dancing" of each source and its intensity fluctuation. These measurements are processed and communicated bi-directionally using a built-in wireless link. The unique geometry of PROPS enables resolution of changes in turbulence along the path resulting from the surface features along that path. PROPS processing also estimates cross-wind speeds as seen from both sides of the path. PROPS automatically collects, processes, catalogs, and reports these data for future reference. Output data is uniquely formatted to enable theoretical turbulence calculations and for customized wave-optics simulations



DELTA Imaging Path Turbulence Monitor, PM-02-600


Applications Passively monitors turbulence conditions

- Laser propagation path characterization
- Atmospheric imaging diagnostics
- Ontical communications link performance
- Evapo-transpiration and water management
- Include turbulence profiles in wave-optics simulations
- Enables custom MATLAB analysis

Unique Advantages

- Bounds C_² turbulence strength along path
- · Automatic computation of:
 - Rytov number Scintillation index
 - Fried's coherence diameter
 - Isoplanatic angle
 - o Cross-wind speeds
- Greenwood and Tyler frequencies · 2 km range from target to receiver
- Automatic collection, processing, and reporting of turbulence diagnostics
- Portable and compact system
- Passive operation—no external sources
- required for diagnostic target
 - Output supports ATMTools and WaveTrain

The DELTA system is place at one end of the path, with a target or object with multiple, trackable features on the opposite end. Depending on the size of the target and the optics on the telescope, a range of % to 2 kilometers can be achieved. Once initial setup has been conducted, user desired parameters are adjusted such as feedback period, duration of observation and stored output info. A sequence of imagery is collected and the deviation or "dancing" of feature points on the target is recorded. The DELTA method measures the differential jitter of feature pairs as a function of angular separation. Using multiple pairs at various degrees of separation, a non-uniform Cn2 profile is estimated using additional atmospheric estimation software. Turbulence statistics are calculated from this profile, as well as cross-wind speeds






DELTA Atmospheric Characterization Model: PM-02-600, Single-Ended




- Passively monitors turbulence conditions
- Provides C_n² bounds over propagation path
- Provides wind speed
- Compact and portable
- Output atmospheric diagnostics compatible with ATMTools and WaveTrain



RWPII - 01/2018



Dual-Ended Path-Resolved Turbulence Profilers






- Estimates C_n² values in bins along a line-ofsight
- Assists in understanding of optical system propagation performance including fades, dropouts, bit error rate (BER), etc.

Terminal B . telescope and source • assembly

Applications

- Laser propagation path characterization
- Atmospheric imaging diagnostics
- Optical communications link performance
- Evapo-transpiration and water management
- Include profiles in waveoptics simulations
- Enables custom MATLAB analysis



Model: PR-50-1500, Range: up to 200 km

Model: PR-05-600, Range: 0.5 - 5 km




Atmospheric Characterization Devices Export/ITAR Controls

- Commodity Jurisdiction (CJ) determinations have established that the Atmospheric Turbulence Profilers and Diagnostic products are regulated by the EAR and most are classified as EAR99.
- PROPS Model PR-05-600 can be exported without restriction.
- MZA has not received a CJ on DELTA Model PM-02-600, but because it is a fundamentally simpler device, believe that when completed, the CJ will find the device to be EAR99.
- The distinction with respect to the exportability of the PROPS devices seems to be the range at which the device can operate and the use of lasers (as opposed to LEDs) as sources.



High-Speed Optical Tracker and Adaptive Optics System



 Full system including deformable mirror, high-speed wavefront processor, and track+AO controls built by MZA



North Oscura Peak Facility


MZA...

- Developed the specifications for the 1-meter telescope and then assisted in its procurement and installation.
- Designed and implemented the Coude path.
- Designed illuminator insertion optical path.
- Implemented numerous embedded systems for atmospheric characterization, system monitoring, safety, and diagnostics.






Predictive Control for AO







Sparse Aperture Image Synthesis, **Compensation, and Tracking Processor**

- **High-bandwidth processing** capability required for phased array imaging applications
- Spatial-heterodyne imaging provides complex field data allowing for fully <u>digital</u> phasing
- Parallel GPUs give significant performance boost over CPUs
- **COTS** hardware







50

60



(http://www.activeopticalsystems.com/)

MZA's beam control hardware component affiliate.

- MZA created Active Optical Systems, LLC (AOS) to develop and commercialize low-cost, compact adaptive optics components.
- AOS manufactures deformable mirrors for low and very high power laser applications.
- AOS also provides numerous types of optical sensors intended to provide wave front control (beam shaping) and aim point maintenance.
- AOS uses the latest COTS technology to reduce the cost of implementing high-performance computer control systems.

The DSB identified a need in the U.S. directed energy industrial base for beam control and deformable mirrors.

Defense Science Board Task Force on Directed Energy Weapons



December 2007

Office of the Under Secretary of Defense For Acquisition, Technology, and Logistics Washington, D.C. 20301-3140


- The lack of directed energy production programs or the serious prospect of significant production programs has jeopardized the supporting industrial base. There is essentially one U.S. vendor capable of supplying deformable mirrors.
 - The Deputy Secretary of Defense should direct the military departments to provide overall vision and strategic plans for developing relevant directed energy capabilities that can provide visibility into the likely future business case for sustaining directed energy industry capabilities.
- The nation's technical capabilities in HEL components and subsystems are thin and have, in some cases, atrophied. The situation in large high-power optics and beam control is particularly fragile depending on a single vendor at best.

USD (AT&L) should direct a survey of laser component capability and produce a plan for sustaining access to the required capability.

MZA and AOS have stepped up to this challenge. We are now the second US provider of high power deformable mirrors. We have also significantly improved the state-of-the-art in beam control systems engineering.

MZA/AOS High Power Deformable Mirrors

- 100 kW average power for up to 5 seconds over a 6 cm² area with < 1 deg. C temperature increase.
- Tested up to 250 kW CW.
- Rapid fabrication possible.
- More than 50 high power DMs delivered






We offer complete systems that include the DM, compact high-voltage drive electronics and full adaptive optic feedback control systems.




Develops and manufactures adaptive optics components and systems






Overview of Modeling & Analysis Capabilities







<u>Scaling for High Energy Laser</u> and <u>Relay Engagement (SHaRE)</u>



Load into Excel

Irradiance Analysi


- Original development sponsored by AFRL/DE Relay Mirror Program
 - OAFRL/RD approves distribution

OMATLAB toolbox for Govt & Govt Contractors

- Used to model <u>strategic</u>, <u>tactical</u>, <u>ground-based</u>, and <u>maritime</u> direct attack and relay HEL systems
 - O Based on work for MDA (BMDO), 2001
 - O Built on ~10 years of scaling law modeling for ABL
 - O Scaling law approaches augmented or innovated for relay uplink
- Modularity supports the addition of new effects and anchoring of isolated and composite relations to both wave-optics and experimental results.
- Enables consideration of wide range of physical effects on laser performance
 - O Laser: power, wavelength, beam quality
 - O Platform: transmitter, jitter, aero-optical
 - OAtmosphere: extinction, turbulence, thermal blooming
 - O Beam control: finite bandwidth, anisoplanatism, sensor SNR
 - OTarget: velocity, engagement geometry




- Beam control metrics take into account the transmission losses, aimpoint error, and beam spread due to jitter and higher-order effects.
- The instantaneous power is projected onto the vulnerable region of the target.
- The power is then integrated in space and time to compute a fluence on target.
- Target vulnerability criteria are applied to determine whether and when sufficient fluence has been deposited on target.






Tactical Beam Control Error Tree


SHaRE generates error trees which can be customized to support requirements analysis and flowdown for a given system design.



Wave optics made easy ier

The Challenge of Wave Optics Simulation Wave optics simulation is a crucial technology for the design and development for advanced optical systems. Until now it has been the sole province of a handful of specialists because the available codes were extraordinarily complicated, difficult to use, and they often required supercomputing resources.






The Solution is WaveTrain


WaveTrain puts the power of wave optics simulation on your PC. Through an intuitive connect-the-blocks visual programming environment, you can assemble beam lines, control loops, and complete system models, including closed-loop adaptive optics (AO) systems.





A Basic WaveTrain Model





Starfire Optical Range (SOR) imaging and adaptive optics model.



Dynamic Runs

Track and Science

x 10⁵ × 10 **Major Parameters:** 18 **Runsets:** 20 20 SOR3501Runbs1 16 10 1 x Clear-1 atmosphere. 14 40 40 Wind was 5 m/s at low 12 60 altitudes and 15 m/s at high 60 10 altitudes. 8 80 80 10 phase screens. 256x256 propagations with 100 100 0.04 cm spacing. Strehl is 0.36 120 120 Point source beacon 20 60 80 100 120 60 80 100 40 <u>4</u>0 120 Dual point sources separated Average Uncompensated Track Image **Average Compensated Track Image** at 0.3 arcsec. as celestial x 10⁶ x 10' objects. 100 16 4 Resolved wavefront sensor 0.3 arcseconds 14 (instead of 2x2 quad cell) 50 3.5 110 Est. AO closed-loop system arcseconds 12 3 bandwidth is about 50 Hz 120 100 10 at -3dB 2.5 Est. Track closed-loop system 8 2 130 150 bandwidth is about 240 Hz 1.5 6 at -3dB. 3.2 140 1 4 200 Peak is 38 times greater than uncompensated. 0.52 150 250 50 150 200 100 250 110 120 130 140 100 150 **Average Compensated Science Image Average Uncompensated Science Image**

RWPII – 01/2018

(zoomed)



Wavefront Compensation

Static Run – Field and DM

Major Parameters:

Runset: SOR3501Runa1w0

1 x Clear-1 atmosphere with no wind.


10 phase screens.

512x512 propagations with 0.02 cm spacing.


Point source beacon

Dual point sources separated at 0.3 arcsec. as celestial objects.

Resolved wavefront sensor (instead of 2x2 quad cell)



20 100 120 140 160 20 40 60 80 100 120 140 160 **Initial Uncompensated Pupil Phase**



-2




Wavefront Sensor Model

Static Run – WFS

Major Parameters:


- Runset:
 - SOR3501Runa1w0
- 1 x Clear-1 atmosphere with no wind.
- 10 phase screens.
- 512x512 propagations with 0.02 cm spacing.
- Point source beacon
- Dual point sources separated at 0.3 arcsec. as celestial objects.
- Resolved wavefront sensor (instead of 2x2 quad cell)




RWPII – 01/2018

Comparison with Published SOR Results

First light for the adaptive optics system on the 3.5-m telescope at the Starfire Optical Range occurred in September, 1997. This astronomical I Band compensated image of the binary star k-Peg was generated using the 756 active actuator adaptive optics system.



Uncompensated Image



Compensated Image. 0.3 arcsec separation





Simulated Data

Actual Data

are not available.

From the SOR website.

Atmospheric conditions, camera characteristics, and control loop parameters


Runsets: SOR3501Runa1w20 & SOR3501Runa1w20ol

1 x Clear-1 atmosphere.


Wind was 20 m/s at all altitudes.

10 phase screens.


512x512 grid with 0.02 cm spacing.




35



Air-to-Ground Laser Comm System




Laser Comm Terminal Adaptive Optics Increases Power Transmission from Transmitter to Receiver





Phased-Aperture Imaging Concept




- We've developed new concepts for phased-aperture imaging.


-The concepts can also be extended perform to phasedaperture beam projection.




Overview of Laser Resonator Design and Analysis Capabilities

Laser Modeling with WaveTrain











Massively Multi-Mode Stable Laser Modeling


- MZA developed a new theory of numerical mesh requirements for stable resonators.
 - **O** Reduces the computational requirements required for accurate modeling.
- MZA developed a technique for modeling multi-transverse modes that stabilized the power and matched with Rigrod theory.





- MZA developed an approach for mesh determination for unstable laser resonators
 - O Based on ray-optics
 - Reduces mesh size
- Diffraction Core
 - **O** Radial Streaking
- Magnify & Add
 - Aberrations in a resonator amplify & down-sample in spatial frequency
- Anchoring








Fiber Laser Modeling

• Fiber Laser Amplifier Modeling including


ORate Equation Gain

- O Amplified Spontaneous Emission (ASE)
- O Rayleigh Back-Scattering
- Stimulated Brillouin Scattering (SBS)






RADICL Stable Resonator Modeling with GASP CFD



LOCSET Fiber Phasing Concept

First Experimental Demonstration of Self-Synchronous Locking of Optical Coherence by Single-detector Electronic-frequency Tagging of Fiber Amplifiers

T. M. Shay^a, Vincent Benham^b, J. T. Baker^c, Capt. Benjamin Ward^a, Anthony D. Sanchez^a, Mark A. Culpepper^a, Sgt. D. Pilkington^a, Lt. Justin Spring^a, Lt. Douglas J. Nelson^a, and Lt. Chunte A. Lu^a



Summary of Laser Source Modeling

- Wave-optics Models of Laser Resonators
 - ABL COIL Modeling (for ABL SPO)
 - RADICL Modeling (for AFRL)
 - SSL Modeling (for Textron JHPSSL & HELLADS)
 - Integration with GASP (for AFRL)
 - Fiber Laser Illuminator Modeling (for AFRL)
- Engineering Models
 - LADERA JHPSSL Specifications (for HEL JTO)
 - LADERA SSL System Weight Model (for AFRL)
- Fiber Physics and Control Modeling
 - Detailed Fiber Amplifier Modeling (for AFRL)
 - LOCSET Fiber Phasing Control Algorithm (for AFRL)





Overview Of **Adaptive Optics and Wavefront Compensation** for **High Energy Laser Weapons Systems** (HELWS) and **Optical Surveillance Systems**



Adaptive Optics Systems Make HELWS More Lethal and Cost Effective

• High Energy Laser Weapons Systems must...

O employ a Laser Source of sufficient power to be lethal, and
O be projected from a Beam Director of sufficient diameter.

• The Laser Source and the Beam Director make up nearly all of the Size, Weight, and Power required by a HELWS

• The logistical footprint of a HELWS can become significant.

• The addition of Adaptive Optics to a HELWS allows...

- a lower power Laser Source to achieve the same lethality as that of a system with a lower laser power source.
- a smaller Beam Director to achieve the same lethality and better surveillance capabilities as that of a system with a larger Beam Director.

• The most cost effective High Energy Laser Weapons Systems will employ Adaptive Optics.



• Extends the range

• Adaptive Optics Wavefront Compensation delivers more power to a target vulnerable region at longer ranges.

Reduces the time-to-kill

- More power on the target vulnerable region means that it takes less time to kill the target
- This allows greater margin in the system and possibly increases the number of defeated targets in a salvo.

Reduces the total number of systems in an area defense

• Increased range and decreased time means that fewer total weapons system might be used to defend the same area.

Increases system robustness

• The presence of an adaptive optics system potentially increases the range of environmental conditions under which the system can be effective.

Improves surveillance range and quality

• Adaptive optics improves image quality when the system is used for surveillance purposes.

Adaptive Optics Systems Increase the Resolution and Quality of ISR Systems

Optical surveillance systems must...

O contend with intervening atmospheric distortions,

O and operate under a range of vibration and thermal conditions.

• The typical approach to improving such systems is to...

- O increase the aperture diameter,
- O constrain the operational environment, and

O employ more expensive sensors.


 These approaches all increase the cost, complexity, and logistical footprint.

• The addition of Adaptive Optics to such systems allows...

O the same aperture diameter to achieve greater effective resolution, and
O increase the signal-to-noise ratio on the optical sensors.

• The most capable future ISR systems will employ Adaptive Optics.


The Need for Wavefront Compensation



target vulnerable region.




Target Illumination






Wavefront Measurement






Deformable Mirror Shaping




High Energy Laser Illumination





Surveillance and Imaging





MZA Associates Corporation

An Employee-Owned Company

Laser Weapon & Sensing Modeling and Simulation Laser System Testing and Integration Adaptive-Optics Beam Control Hardware

Contact: Robert W. Praus, II President 2021 Girard Blvd. SE, Suite 150 Albuquerque, NM 87106

Robert.Praus@mza.com (505) 245-9970, ext. 111